



FEATURES:

- ✓ Mounts in panels from .070" to .375" (1.60mm to 9.53mm).

MATERIALS:

- Banana Jack: Bright Tin Plated Brass
- Mounting Base: Polycarbonate
- Insulator: Polycarbonate
- Lockwasher: Nickel Plated Steel
- Hex Nut: 3/8" 1/4-32 Nickel Plated Brass
- Solder Turret: Bright Tin Plated Brass

RATINGS:

- Operating Voltage: Hands free usage in controlled voltage environments: 2500 Vrms maximum. *For CE compliance:* not intended for hand-held use at voltages above 33 Vrms/70 Vdc.
- Operating Temperature: +239°F (+115°C) Max.
- Current: 15 Amperes

ORDERING INFORMATION:
 Model 2269-0 (Black Base)
 Model 2269-2 (Red Base)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[2269-2](#) [2269-0](#) [2269-0#](#)