



### FEATURES:

- ✓ Gold or Tin Plated
- ✓ Panel Thickness .07 (1,78mm) to .170" (4,32mm)
- ✓ Accepts miniature banana plug, wire or spade lug..
- ✓ Hardware Included

### MATERIALS:

*Insulated Captive Thumb Nut:*

- Model: 2382, Gold Flash Brass;
- Model 2439, Tin Plated Brass

*Binding Post Body:*

- Model: 2382, Gold Plated Brass
- Model: 2439, Tin Plated Brass

*Solder Turret Terminal:* – Gold Flash; 2439 - Tin

- Model: 2382, Gold Flash Brass
- Model 2439, Tin Plating Brass

*Thumb Nut, Mounting Base and Insulator:*  
Polycarbonate.

*Lockwasher:* Nickel Plated Steel

*Hex Nut 1.4" #8-32:* Nickel Plated Brass

### RATINGS:

Operating Voltage: Hands free usage in controlled voltage environments: 1500 Vrms maximum.  
*For CE compliance:* not intended for hand-held use at voltages above 33 Vrms/70 Vdc.

Current: 5 Amperes

Operating Temperature: +115°C (+239°F) Max.

### ORDERING INFORMATION:

Model 2382-**Color** (Gold)

Model 2439-**Color** (Tin)

**Color** = 0 (Black), 1 (Brown), 2 (Red), 3 (Orange),  
4 (Yellow), 5 (Green), 6 (Blue), 7 (Violet), 8 (Gray) 9 (White)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)  
For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[2382-8](#) [2382-7](#) [2382-4](#) [2382-9](#) [2382-3](#) [2439-4](#) [2439-7](#) [2439-8](#) [2439-3](#) [2439-9](#)