



### MATERIALS:

Body and Fittings: Brass, Tarnish Resistant Plating

Center Contact: Gold Plated Beryllium Copper

Dielectric: PTFE

Finish: Body and Fittings: Tarnish Resistant

Center Contact: Gold Plated

### RATING:

Nominal Impedance: 50 Ohms

Operating Temperature:  $-65^{\circ}\text{C}$  to  $+165^{\circ}\text{C}$

### ORDERING INFORMATION: Model 2451

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02''$  (.51 mm),  $.xxx = \pm .005''$  (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[2451#](#)