




MATERIALS:

Body: Gold Plated Brass
Center Contact: Gold Plated Beryllium Copper
Dielectric: PTFE

Finish:

Body: Tarnish Resistant
Center Contact: Gold Plated

RATINGS:

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)
Operating Voltage: 1000 VRMS
Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 2455

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[2455#](#)