



FEATURES:

- This telephone plug is commonly used in switching panels and telecommunication equipment.
- Readily adapts telecommunication equipment for connection to BNC coaxial cables.
- Only the tip and ring are connected. The tip is connected to center contact and the ring is connected to the shell of the BNC. The sleeve is floating.

MATERIALS:

BNC: Outer shell is brass with tarnish resistant plating. Center contact is Beryllium Copper with gold plating.

Plug: Brass with black ABS insulation. Marking: "Model 2798"

RATINGS:

Operating Voltage: 500V (Disconnect power before handling)

Operating Temperature: +50°C (+122°F) Max.

ORDERING INFORMATION: Model 2798

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[2798](#)