



FEATURES:

- ✓ Converts BNC (Female) cables / connectors to alligators for test versatility.
- ✓ BNC connector is molded directly to the wire for pull strength durability and dust and moisture resistance.
- ✓ BNC center contact is gold plated brass for corrosion resistance, low contact resistance and long insertion life.
- ✓ Alligator clips attach to terminals up to .300" (7.6mm) diameter.
- ✓ Black wire is connected to BNC shell, red wire to BNC center contact.

MATERIALS:

BNC: Nickel Plated Brass, Center Contact: Gold Plated Brass

Dielectric: PTFE

Wire: 18 AWG, PVC Insulated

Alligator: Nickel plated steel, Spring: stainless steel

Boot: Vinyl, color matches color of wire

RATINGS:

Operating Voltage: Hands free testing in controlled voltage environments: 150 VRMS Max.

Operating Temperature: +122°F (+50°C) Max.

ORDERING INFORMATION: Model 2885*

* Custom lengths are available, contact Pomona Product Support at: 1-800-241-2060

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[2885](#)