



FEATURES:

- ✓ Fits standard banana jack

MATERIALS:

- Banana Plug Body: Brass, Alloy 360, 1/2 Hard
- Spring: Beryllium Copper, Berylco 25, Cond. H.T.
- Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches
- Screw: Model 3265 - 6-32 x .25" (6,35mm) Pan head, Phillips, steel, nickel plated
 Model 3266 - 8-32 x .25" (6,35mm) Pan head, Phillips, steel, nickel plated.
- Solder Lug: Copper per QQ-C-576
- Finish: Electro tin plated

RATINGS:

- Voltage: Hands free testing in controlled voltage environments: 500 Vrms Max. *For CE compliance: not intended for hand-held use at voltages above 33 Vrms/70 Vdc.*
- Current: 15 Amps

ORDERING INFORMATION:

- Model with 6-32 screw: 3265
- Model with 8-32 screw: 3266
- Sold in package of 10

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3265 3266