



FEATURES:

- Fits standard banana plug.
- 1/4 - 32 Thread

MATERIAL:

Banana Jack Body – Nickel Plated Brass

Solder Lug – Copper, finish – Hot tin dip

Hex Nut – Brass - 6.35 (.250) –23 Double Chamfered, Nickel Plated

RATING:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 2500 WVDC Max.

Current: 15 Amperes Cont.

ORDERING INFORMATION: Model 3267

All dimensions are in inches. Tolerances (except noted): .xx = \pm .02" (.51 mm), .xxx = \pm .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3267#