



FEATURES:

- Mounts in panels from 1.57 (.062) to 6.35 (.250) thick.
- Crosshole is perpendicular with flat on mounting base.

MATERIALS:

Insulated Captive Thumb Nut: Brass

Insulation: Polycarbonate

Mounting Base: Polycarbonate

Insulator: Polycarbonate

Lockwasher: Steel

Hex Nut: Brass

Binding Post:

Finish: 3750 – Gold plated brass

3760 – Bright tin plated brass

3770 – Gold plated Tellurium Copper

RATINGS:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 2500 WVDC Max.

Operating Temperature: +115°C (+239°F) Max.

Current: 15 Amperes

ORDERING INFORMATION: Model 3770-*

*=Color, -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

Ordering Example: 3770-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3770-6](#) [3770-7](#) [3770-5](#) [3770-4](#) [3770-9](#) [3770-1](#) [3770-3](#) [3770-8](#) [3760-02](#)