



MATERIALS:

Connector:

Body: Tarnish Resistant Plating, Center Contact: Gold Plated Beryllium Copper

Shielded Housing: Die cast aluminum, Alloy A380 or A384

Cover: .040 thick aluminum alloy 1100-H14

Screws: Steel. 4 each 2-32 x 1/4" pan head, self-tapping

Finish:

Shielded Housing – None

Cover – Clear anodized

Screws – Zinc per ASTM B633-85, Type II (bright blue)

RATINGS:

Operating Temperature: -55°C to +150°C

ORDERING INFORMATION: Model 3754

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[3754](#)