



FEATURES:

- Permits BNC male to be used with equipment having tini jacks.
- Readily adapts equipment to available BNC coaxial cables.
- All metal construction to insure proper shielding.

MATERIALS:

Upper Conn: BNC Female

Body and Fittings: Tarnish resistant.

Center Contact: Gold plated per requirements of MIL-C-39012.

Adapter Body:

Material: Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Marking: "POMONA ELECTRONICS MODEL 3837."

Lower Conn: Tini Plug

RATINGS:

Operating Temperature: -55° C. to +125° C. (-67° F. to +257° F.)

Operating Voltage: 500 VRMS.

ORDERING INFORMATION: Model 3837

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[3837](#)