



MATERIALS:

Body and Fittings - Brass
Center Contact – Gold Plated Brass
Connector meets the interface requirements of MIL-STD-348.
Gasket: Silicone rubber

Finish:

Body and Fittings – White Bronze Plating
Center Contact – Gold Plated Brass

RATINGS:

Operating Voltage: 1000 VRMS
Nominal Impedance: 50 Ohms
Dielectric – PTFE

ORDERING INFORMATION: Model 3842

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3842