



MATERIALS:

Body and Fittings - Brass
 Center Contact (Male) – Gold Plated Brass
 Center Contact (Female) – Gold Plated Beryllium Copper
 Outer Contact (Male) – Gold Plated Brass
 Gasket/Seal – Silicone Rubber

Finish:

Body and Fittings – White Bronze Plating
 Center Contact (M) – Gold Plated Brass
 Center Contact (F) – Gold Plated Beryllium copper
 Outer Contact (M) – Tarnish Resistant

RATINGS:

Operating Voltage: 1000 VRMS
 Nominal Impedance: 50 Ohms
 Dielectric – PTFE

ORDERING INFORMATION: Model 3843

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3843#