



### FEATURES:

- Mounts in panels up to  $.175$  (4,45) thick.
- BNC shell body isolated from threaded flange.

### MATERIALS:

Body – Brass, Tarnish Resistant Plating, Center Contact: Gold Plated Beryllium Copper

Dielectric: PTFE

Center Contact – Gold Plated

Marking: “Pomona 3846”

### RATINGS:

Operating Voltage: Inner Conductor/Shield: 500VRMS Max.

Operating Temperature:  $-65^{\circ}\text{C}$  to  $+165^{\circ}\text{C}$

Nominal Impedance: 50 Ohms

### ORDERING INFORMATION: Model 3846

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$  (.51 mm),  $.xxx = \pm .005$  (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90215 (800) 444-6785 or (425) 466-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[3846](#)