



#### MATERIALS:

Molded Housing and Cover: Glass filled nylon.

Screws: Steel, 4 each, #2-32 x 1/4, Pan Head, self-tapping

#### RATINGS:

Operating Temperature: +216°F (+102°C)

#### ORDERING INFORMATION: Model 3850-Color

Model 3850-0 (Black)

Model 3850-6 (Blue)



All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 425-446-5844 Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)

For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3850-0](#) [3850-6](#)