



### MATERIALS:

Molded Housing and Cover: Glass filled nylon. Color: See Tab Block.

Marking: POMONA ELECTRONICS 3850

Screws: Steel, 4 each, #2-32 x 1/4, Pan Head, self-tapping

### RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

### ORDERING INFORMATION: Model 3850-\*

\* = Color, -0 Black, -6 Blue, -9 White.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3850-9