



FEATURES:

- Converts equipment with two conductor .097" diameter. micro jacks for use with BNC cables
- The all metal construction allows operation in higher temperature environments

MATERIAL:

Body: Brass, corrosion resistant plating

Center Contact: Beryllium Copper, gold plating

RATINGS:

Operating Temperature.: +257° F. (+125° C.) Max.

Operating Voltage: 500 VRMS Max.

ORDERING INFORMATION: Model 4267

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4267](#)