



MATERIALS:

Body: Gold Plated Beryllium Copper,
Male Contact - Gold Plated Brass,
Female Contact – Gold Plated Beryllium Copper

Dielectric: Teflon per L-P-403

Finish: Body and Contacts – Gold plated per MIL-G-45204, Type II, Class 2

Marking: “Pomona 4293”

RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 335VRMS Max.

Nominal Impedance: 50 Ohms

Frequency Range: 0-12.4 GHz.

Operating Temperature: -65°C (-85°F) to (+329°F)

ORDERING INFORMATION: Model 4293

All dimensions are in inches. Tolerances (except noted): .xx = $\pm.02$ " (.51 mm), .xxx = $\pm.005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4293](#)