



### MATERIALS:

Body: Gold Plated Beryllium Copper, Center Contacts: Gold Plated Beryllium Copper

Finish: Body and Contact – Gold plated per MIL-G-45204, Type II, class 2.

Marking: “Pomona 4295”

### RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 335VRMS Max.

Nominal Impedance: 50 Ohms

Frequency Range: 0-12.4 GHz.

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

### OPERATING INFORMATION: Model 4295

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4295