



MATERIALS:

Contact – Beryllium Copper, Alloy 165, ½ HM.

Spring – Stainless Steel, 302

Sq. Pin – Phosphor Bronze, Alloy 510

Finish:

Contact & Sq. Pin – Gold plated per MIL-G_45204, Type II, Class 00 over nickel.

Insulation: Glass filled nylon.

Marking: “POMONA GRABBER® 4521”

Overall Length: 1.73”

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

Operating Voltage: 150 VRM/DC

Current: 3 Amperes

ORDERING INFORMATION: Model 4521-* & Model 5925 Kit

* = Color, Standard Colors: -0 Black, -2 Red

Kit 5925 contains 10 pieces of 4521 clips, one of each color: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4521-0](#) [4521-2](#)