



FEATURES:

- Ideal for providing jumper wires between small components.

MATERIALS:

Conn: 1st End - Micrograbber®

Material: Contact – Beryllium Copper per QQ-C-533, Alloy 165, ¼ HM.

Spring – Stainless Steel, Alloy 302.

Finish: Contact – Gold plated per MIL-G-45204, Type 1, Class 00.

Insulation: Glass filled nylon.

Marking: “POMONA ELECTRONICS” “MICROGRABBER®”

Wire: 20 AWG, stranding 41 x 36 t.c., PVC insulated 2.21 (.087) O.D.

Marking: “POMONA 4613-”

Color: See Ordering Information.

Conn: Same as first end.

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

Operating Voltage: 30VAC/60VDC Max.

Current: 3 Amperes

ORDERING INFORMATION: Model 4613-XX-*

Single Patch Cord: XX = Cable Lengths, Standard Lengths: 12” (305), 24” (610), 36” (914) & 48” (1219).

Additional lengths can be quoted upon request.

Ordering Example: 4613-48-2 Indicates 48” in length, color is Red

ORDERING INFORMATION: Model 5525

Kit containing 10 pieces of Model 4613-24, one of each color.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4613-2