



FEATURES:

- Use for balanced line 2 conductor shielded cable assemblies

MATERIALS:

Upper Connector: Miniature Triple Banana Jack – Brass, H.H. per QQ-B-626, Alloy 360

Finish: Gold plated per MIL-G-45204, Type II (.00001 min.)

Insulation: ABS per L-P-1183, Type II, molded to banana plug bodies

Color: Black and Red

Marking: POMONA ELECTRONICS, CALIF. 4653

Lower Connector: Miniature Triple Banana Plug

Spring: Beryllium Copper, Berylco 25 per QQ-C-533

Plug Body: Brass, H.H., per QQ-B-626, Alloy 360

Finish: Gold Plated per MIL-G-45204, Type II, (.00001 min.)

RATINGS:

Operating Temperature: +50°C (+122°F) Max.

Operating Voltage: 2500 VDC

Current: 5 Amperes

ORDERING INFORMATION: Model 4653-*

+ = Color, Standard Colors: -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4653-0