



MATERIALS:

Connector: 5 ea. BNC Female.
 Nominal Impedance: 50 Ohms
 Finish: Tarnish Resistant
 Screw/Solder Turret: 2 ea. #4-40. Steel
 Housing: Die cast Aluminum, Alloy A380 or A394.
 Finish: Blue paint per Federal Standard 595, #25109 over Phosphoric etch
 Marking: POMONA ELECTRONICS, CALIF.
 Cover: 16.0 (.063) thick Aluminum Alloy 1100-H14 pr QQ-A-250/1.
 Finish: Clear Anodized
 Screw: 4 ea. #2-32 x 1/4" pan head, self-tapping. Steel

RATINGS:

Operating Temperature: -55°C. to +150°C. (-67°F. to +302°F.)

ORDERING INFORMATION: Model 4656

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4656](#)