



**FEATURES:**

- This patch cord can be used as a jumper between 0.6 (.025) sq. pins and equipment with 2.0 (.080) dia. pin jacks.

**MATERIALS:**

Conn: Pin Tip Plug

Material: Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Gold plated per MIL-G-45204, Type II, Class 00, over electroless nickel per MIL-C-26074, Class 1, (.0002/.0003).

Insulation: Polypropylene molded to plug body and wire.

Color: Matches color of wire.

Marking: “POMONA ELECTRONICS POMONA CALIF.”

Wire: 22 AWG, stranded, 19 x 34 T.C., PVC insulated, 1.63 (.064) O.D.

Color: See Ordering Information. Marking: “POMONA 4772-XX”

Conn: .64 (.025) Square Pin Receptacle

Material: Phosphor Bronze.

Finish: Gold Plated

Housing Insulation: Polypropylene

Color: Matches color of wire.

**RATINGS:** Entire Assembly

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 1000 W VDC

Current: 3 Amperes Cont.

**ORDERING INFORMATION:** Model 4772-XX-\*

XX = Cable Lengths, Standard Lengths: 12” (305), 18” (457), 24” (610), 36” (914)

Additional lengths can be quoted upon request.

\*=Color, -0 Black, -2 Red

Ordering Example: 4772-36-2      Indicates 36” in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4772-24-2](#) [4772-24-0](#)