




FEATURES:

- Accepts .080 dia. pin
- Max. panel thickness .25.

MATERIALS:

Pin Jack Insulation: Polycarbonate molded to Pin Jack Body.

Panel Insulator: Polycarbonate. Color matches color of Pin Jack insulation.

Lockwasher #8 Internal Tooth: Steel. Finish: Nickel plated per QQN-290, latest revision, Class 2, 200/300 microinches

Hex Nut #8-32: Brass. Finish: Nickel plated per QQN-290, latest revision, Class 2, 200/300 microinches.

Pin Jack Body: Nickel Plated Brass latest revision, Alloy 360, ½ Hard.

Spring: Gold Plated Beryllium Copper, Berylco 25 per QQC-533, latest revision, Cond. HT.

Finish: Body – Electroless nickel plated per MIL-C-26074, latest revision, Class 2, 200/300 microinches.

Spring – Gold plated per MIL-G-45204, latest revision Type II, Class 00 over electroless nickel per MIL-C-26074, latest revision, Class 1, 200/300 microinches.

Wrapped Wire Terminal: Gold Plated Phosphor Bronze

Finish: Gold plated per MIL-G-45204, latest revision, Type II, Class 00 over electroless nickel per MIL-C-26074, latest revision, Class 1, 200/300 microinches.

RATINGS:

Operating Temperature: +115°C. (+239°F.) Max.

Operating Voltage: 1500 VDC

Current: 3 Amperes

ORDERING INFORMATION: Model 4773-*

* = Color, Standard Colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4773-4](#) [4773-5](#) [4773-9](#)