



### MATERIALS:

Body and Fittings – Brass, Tarnish Resistant Plating, Center Contact – Female: Gold Plated Beryllium Copper, Male: Gold Plated Brass, Outer Contact: Gold Plated Brass  
Dielectric: PTFE

### RATING:

Voltage: Shield/Earth: 30VAC/60VDC Max.  
Inner Conductor/Shield: 500VRMS Max.  
Operating Temperature: -65°C to +165°C  
Nominal Impedance: 50 Ohms

### ORDERING INFORMATION: Model 4896

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4896](#)