



FEATURES:

- Uses a special low-triboelectric cable which has noise attenuating layers surrounding the center conductor.
- The cable is ideal for low power, low frequency measurements.

MATERIALS:

Body: Brass, Tarnish Resistant Plating, Center Contact: Gold Plated Brass

Dielectric: PTFE

Strain Relief: PVC molded directly to cable and connectors

Cable: 22 AWG, stranding 7 x 30 t.c., PVC insulated, 4.95 (.195) O.D.

Marking: "Pomona 4964-SS"

RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +50°C. (+122°F.) Max.

Nominal Impedance: 50 Ohms

Recommended Frequency Range: DC to 10KHz

ORDERING INFORMATION: Model 4964-SS-*

*- Standard Lengths: 12, 24, 26, 48, 60, 96, 120, 144, 180, 240, 300, 360 – Lengths other than those specified are available on special request.

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4964-SS-240](#) [4964-SS-120](#) [4964-SS-60](#) [4964-SS-72](#) [4964-SS-24](#) [4964-SS-48](#) [4964-SS-36](#) [4964-SS-12](#) [4964-SS-26](#) [4964-SS-420](#)