



## FEATURES:

- ✓ Spring-loaded cap captures wire securely for fast connection and release.
- ✓ Mounts in panels from .062" (1.57mm) to .125" (3.18mm) thick.
- ✓ Accepts wire size up to .0925" (2.35mm) diameter.
- ✓ Complies with MIL-P-55149/8.

## MATERIALS:

Body: Nickel Plated Brass

"O" Rings: Silicon Rubber

Cap: Silicon Rubber, Red or Black over body

Hardware: Hex Nut, Split Lockwasher, Brass Washer, Nylon Washer, "O" Rings, Body, Cap

## RATINGS:

Voltage: Hands free usage in controlled voltage environments: 1200 Vrms Max. *For CE compliance: not intended for hand-held use at voltage above 33 Vrms/70 Vdc.*

Current: 15 Amperes

Temperature: +239°F (+115°C) Max.

## ORDERING INFORMATION:

Model 4995-0 (Black)

Model 4995-2 (Red)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)

For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4995-0](#) [4995-2](#) [4995-0#](#)