



FEATURES:

- Permits BNC male to be used with equipment having Western Electric 2.3 (.090) video plugs
- Video plug equivalent to WE-090

MATERIALS:

Body and Fittings: Brass per QQ-B-626, Alloy 360, ½ Hard.

BNC Center Contact: Beryllium Copper per QQ-C-530, Cond. H.T.

Video Center Contact: Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish:

Body and Fittings: Tarnish Resistant

Center Contacts: Gold plate per MIL-C-39012

Marking: POMONA ELECTRONICS 5008

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

Operating Voltage: 500 VRMS

Nominal Impedance: 75 Ohms

ORDERING INFORMATION: Model 5008

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5008