



### FEATURES:

- ✓ Converts BNC (male) cables / connectors to a #8 spade lug connector for terminal strip attachment.
- ✓ BNC connector is molded directly to the wire for pull strength durability and dust and moisture resistance.
- ✓ BNC shell is tarnish resistant.
- ✓ BNC center contact is gold plated Beryllium Copper for excellent electrical connection.
- ✓ Black wire is connected to BNC shell, red wire to BNC center contact.

### MATERIALS:

*BNC:* Nickel Plated Brass, Center Contact: Gold Plated Beryllium Copper

*Dielectric:* PTFE

*Wire:* 20 AWG, PVC

*#8 Spade Lug:* Tin-plated copper alloy

*Lug Insulation:* Vinyl, color matches color of wire

### RATINGS:

Operating Voltage: Hands free testing in controlled voltage environments: 500VRMS Max.

Operating Temperature: +131°F (+55°C) Max.

### ORDERING INFORMATION: Model 5051

\* Custom lengths are available, contact Pomona Product Support at: 1-800-241-2060

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[5051](#)