



### MATERIALS:

Body: Brass, White Bronze Plating

Center Contact: Gold Plated Beryllium Copper

Dielectric – PTFE

Finish: Body – Tarnish resistant

Center Contact – Gold Plated

### RATINGS:

Operating Voltage: 1000 VRMS

Nominal Impedance: 50 Ohms

### ORDERING INFORMATION: Model 5089

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5089