



FEATURES:

- Model 5117 Mates to Model # 5109 straight cord female plug.
- Model 5130 Mates to Model # 5125 straight cord female plug.
- Wall or Floor mount receptacle.
- Model 5117 will accept standard 3 pin XLR female plugs.
- Model 5130 will accept standard 5 pin XLR female plugs.
- Durable Zinc Alloy housing.
- Model 5117 Accepts up to 14 AWG.
- Model 5130 Accepts up to 18 AWG.

MATERIALS:

Housing: Zinc Alloy with a nickel finish

Contacts: Bronze with a Tin finish

Ground Tag: Steel

Insulator: Black Polyester

RATINGS:

Operating Voltage: 133 VRMS/DC

Current: 15 Amperes.

ORDERING INFORMATION: Models 5117, 5130

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5117 5130