



FEATURES:

- This in-line banana jack is ideal for making patch cords and field repairs.
- A snap-on two piece design allows the wire to be crimped or soldered to the banana jack
- Part will accept 18, 20, 22 AWG wire, crimp or solder connection.
- Use with Model #5169 to build a custom extension cable.

MATERIALS:

Body: Brass per QQ-B-626, Alloy 360, ½ Hard.

Insulation: Flexible PVC.

Marking: "POMONA"

Finish: Body – Nickel plated per QQ-N-290, Class 2, 200/300 micro-inches.

RATINGS: (Independent of Wire)

Operating Temperature: +50°C.(+122°F.) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 5000 WVDC Max.

Current: 15 Amperes

ORDERING INFORMATION: Model 5167-*

*= Color, -0 Black, -2 Red

Ordering Example: 5167-0, Color is Black

Other colors available on special request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5167-0](#) [5167-2](#) [5167-0#/BULK](#)