



FEATURES:

- Supports 18 20 & 22 AWG wires.
- This in-line 2.0 (.080) dia. pin tip plug is ideal for making patch cords and field repairs
- Parts will accept 18, 20, 22 AWG wire, crimp or solder connection.
- A snap-on two piece design allows the wire to be crimped or soldered to the pin tip plug.

MATERIALS:

Material: Brass per QQ-B-626, Alloy 360, ½ Hard

Insulation: Flexible PVC.

Marking: "POMONA"

Finish: Nickel plated per QQ-N-290, Class 2, Sulfate process, 200/300 microinches.

RATINGS: (Independent of Wire)

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 3000 VRMS

Current: 5 Amperes

ORDERING INFORMATION: Model 5173-*

*=Color, -0 Black, -2 Red

Ordering Example: 5173-2 Adapter Color is Red

Parts are packaged one to a bag, unassembled.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5173-2](#) [5173-0](#) [5173-0#](#) [5173-2#](#)