



MATERIALS:

Die Cast Box:

Aluminum die cast, Alloy A380 or A384
Finish: None
Marking: "POMONA ELECTRONICS, CALIF."

Cover:

1.60 mm (.063) thick aluminum Alloy 1100-H14
Finish: Clear anodized
Marking: None

Screws:

4 each, 2-32 X 6.35 MM (.25) long Pan Head, self-tapping
Steel
Finish: Nickel Plated

RATINGS:

Operating Temperature: -55° C. to +150° C. (-67°F. to +302°F.)

ORDERING INFORMATION: Model 5203

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5203