



MATERIALS:

Die Cast Box:

Aluminum, die cast, Alloy 380 or A384

Finish: None

Marking: "POMONA ELECTRONICS, CALIF"

Cover:

1.60 (.063) thick aluminum, Alloy 1100-H14

Finish: Clear anodized

Marking: None

Screws:

4 each 2-32 X 6.35 (.25) long, pan head, slotted, self-tapping
Steel

RATINGS:

Operating Temperature: -55°C. to +150°C. (-67°F. to +302°F.)

ORDERING INFORMATION: Model 5255

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5255