

FEATURES:

- BNC, grabbers and breakout wires are molded directly to the cable for added pull strength.
- BNC Cable breakouts to SMD Grabber® Test Clips for test versatility.
- SMD Grabber® Test Clips features gold plated stainless steel pincer for durability and low contact resistance.

MATERIALS:

BNC (Male): Body: Brass, Nickel Plated

Center Pin: Brass, Gold Plated

Impedance: 50 Ohms

Strain Relief & Molded Breakout: PVC, Color: Black

Breakout Wires: 22 AWG, .064" (1.63mm) O.D.,

Color: One Black, One Red

SMD Grabber: Pincer, Stainless Steel, Gold Plated

Spring, Stainless Steel

Insulation: Nylon 6, Color Matches Wire Color

Cable: RG174/U, Impedance: 50 Ohms Nominal, Capacitance: 30.8 pF/Ft., O.D. 0.100" (2.5 mm) Nom.

RATINGS:

Operating Voltage: 150 VRMS/DC

Operating Temperature: 50°C (+122°F) Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 5304-K-xx

xx = Length in inches, Standard Lengths: 24" (60.96 cm), 36" (91.44 cm)

Custom lengths can be quoted upon request.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5304-K-24](#) [5304-K-36](#)