



FEATURES:

- The SMD Grabber® Test Clip is especially suited for testing surface mounted packages on centers as small as 0.635mm (.025in).
- Pincer-like contact grasps individual legs of SMD's such as the SOIC, SOJ, PLCC, etc.
- Its circular design and small size have been developed for easy use and handling.
- Mates with Model #4772 or 4741 square pin receptacles.

MATERIALS:

1st End:

Contact: Stainless steel, selectively gold plated.

Insulation: Glass filled Nylon

2nd End:

Square pin, phosphor bronze, gold plated.

RATINGS:

Operating Temperature: +102°C (+216°F) Max

Operating Voltage: 30VAC/60VDC

Current: 0.5 Amperes

ORDERING INFORMATION: Model 5360-*

*=Color, -0 Black, -2 Red

Additional colors can be quoted upon request.

Ordering Example: 5360-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5360-2](#) [5360-0](#)