



FEATURES:

- SMD Grabber® Test Clip features gold plated stainless steel pincer for durability and low contact resistance.
- Ideal for jumping to .025" (.64mm) square pins.
- Receptacle is gold plated to optimize the electrical connection.

MATERIALS:

SMD GRABBER: Pincer, Stainless Steel, Gold Plated

Spring, Stainless Steel

Insulation: Nylon 6, Color Matches Wire Color

Wire: 22 AWG, 26 x 36 t.c., PVC Insulation .064" (1.63mm) O.D. Nom.

Receptacle Body – Phosphor Bronze, Gold Plated

Housing: Polypropylene, Color Matches Wire

RATINGS:

Operating Voltage: 150 VRMS/DC

Operating Temperature: +50°C (+122°F)

Current: 0.5 Amperes Max.

ORDERING INFORMATION: Model 5412

Single Patch Cord:

5412-Length-Color Code

XX = Length in Inches, Standard Lengths: 12" (30,48cm), 24" (60,96cm), 36" (91,44cm)

* = Color, Standard Colors: -0 Black, -2 Red

Additional lengths can be quoted upon request.

ORDERING INFORMATION: Model 5924

Kit containing 10 pieces of Model 5412-12, one each of ten colors

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5412-12-2](#) [5412-36-2](#) [5412-36-0](#) [5412-24-2](#) [5412-24-0](#)