



FEATURES:

- Install this miniature probe on the end of any 18 to 22 AWG test lead having a maximum insulation O.D. of .115"

MATERIALS:

Body: Brass

Finish: Nickel Plated

Insulation: Nylon

RATINGS:

Operating Temperature: +80° C. (+176° F.) Max.

Operating Voltage: 1500V AC/DC

Current: 10 Amperes

ORDERING INFORMATION: Model 5432-*

*= Color, -0 Black, -2 Red

Ordering Example: 5432-2 Color is Red

6234 (Kit includes one Black and one Red probe).

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5432-0](#) [5432-2](#)