



FEATURES:

- Ideal for testing SMD components.
- Two pairs of tweezers may be used as Kelvin leads with 4-wire test instruments.
- Sleeved banana plugs for mating to double insulated banana jacks.

MATERIALS:

Conn: Sleeved Banana Plug

Body: Brass

Spring: Beryllium Copper spring, nickel plated.

Insulation: Flexible PVC.

RATINGS:

Operating Temperature: 122°F. (50°C)

Operating Voltage: 400 VRMS/DC

Current: 3 Amperes Max.

ORDERING INFORMATION: Model 5678

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[5678-K-48](#)