



FEATURES:

- Mates with Model #'s 4771, 4772 or 4741 square pin receptacles.
- The rotating Micrograbber® Test Clip is ideal for testing surface mounted devices (SMDs), high density leads with 1.2 (0.05) spacing, and fine gauge wires 0.1 (0.004).
- Two access entries with 0.6 (.025) square pins.
- Rotating pincers grasp leads firmly.
- Extended guide tube reaches into right areas and can be bent to a 35° angle.

MATERIALS:

Insulation: Nylon

Wire: Steel

RATINGS:

Operating Temperature: +80°C (+176°F) Max

Operating Voltage: 33 VRMS / 70 VDC

Current: 2 Amperes Max

ORDERING INFORMATION: Model 5790-*

*=Color, -0 Black, -2 Red

Ordering Example: 5790-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5790-0](#) [5790-2](#)