



FEATURES:

- Maxigrabber® test clip has been redesigned to meet IEC 1010-2-31. This is the latest international safety standard for test accessories.
- The long shaft is ideal for electronic, electrical and industrial applications where access to hard to reach high voltage test points is a requirement.
- Clip jaws securely grip wires and test points for solid contact with conductors.
- Safety sheathed jack mates to Pomona's 5907A, 5908A and 5909A Flexible Test Leads for Digital Multi-Meter interfacing.

MATERIALS:

Jaws: Brass, Nickel Plated

Plunger, Housing: Polypropylene, Color: One Black, One Red

Banana Jack: Body - Brass, Nickel Plated

Compression Spring: Stainless Steel

RATING:

IEC 1010, Category III, P2 Compliant

Operating Voltage: 1000 VRMS/DC

Operating Current: 10 Amperes Max.

ORDERING INFORMATION: Model 5912B (Includes Set of one black and one red)

The Maxigrabber® Test Clip is also available in various Pomona DMM Test Kits.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5912B