



FEATURES:

- Extra large jaw opening (1") for use in industrial and automotive applications
- Conforms to IEC 1010-2-031
- Mates to Banana Plug Test Leads; Example Pomona Model 5908A

MATERIALS:

Body: Steel, nickel plated

Insulation: Thermoplastic, torsion spring – music wire

Color: One Black, one Red

RATINGS:

Operating Voltage: Category III, 600 VRMS

Current: 10 Amperes

ORDERING INFORMATION: Model 5914

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5914