



FEATURES:

- Kit includes one Oscilloscope probe and below listed accessories.
- Probes are fully insulated for use with Fluke ScopeMeters®, and Portable Oscilloscopes.

RATINGS:

Performance Specifications:

Attenuation:	Bandwidth (MHz)	Input Impedance (MW)	Input Capacitance (pF)	Approx. Rise Time (nS)	Voltage (V Max.) +	Compensation Range (pF)	Cable Length:
X1/X10	20/200	1/10	47/15	17.5/1.8	250	10-60	1.2 Meters

+ Derated with Frequency

ACCESSORIES INCLUDED IN KIT

Description:	Pomona Reordering Part Number:
Full Acc. Kit	6034-2 (Red), 6034-8 (Gray)
Sprung Hook	6095-2 (Red), 6095-8 (Gray)
Trimmer Tool	6096
IC Tip	6097
Insulating Tip	6098
BNC Adapter	5822
Replacement Tip	6099
Ground Lead	5825
Sheathed Banana Plug Adapter	6100

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Pomona®

Model 6035 Fully Insulated Switchable Oscilloscope Probes

ORDERING INFORMATION: Model 6035-* * = Color, -2 Red, -8 Gray

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

6/9/99

SY/EH/LS

C:\Laura Goldberg\FlukeDataSheet\d6035_1_01.doc

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90436 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Page 2 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6035-8 6035-2