



FEATURES:

- Interfaces to safety style sheathed 4 mm plugs.
- Provides a fast and easy method to splice two cables together to increase cable length.
- Complies to IEC 1010-2-031, which is the latest international safety standard for test accessories.
- For added safety, the insulation material is Polypropylene, Fire Retardant – UL94 V-2 rated.
- Mates to Pomona's Models 5907A, 5908A and 5909A flexible test leads.

MATERIALS:

Tubing: Brass, Nickel Plated

Insulation: Polypropylene, Color: One black and one red

RATINGS:

IEC 1010 2-031, Category III, P2 Compliant

Operating Temperature: 80°C (176°F) Max.

Operating Voltage: 1,000 VRMS/DC Max.

Current: 10 Amperes Max.

ORDERING INFORMATION: Model 6252

(Set of one black and one red)

Couplers are also included in many Pomona DMM Test Kits.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6252 6252#