



FEATURES:

- Cable is designed to be used with all standard .166" or 4mm diameter shrouded banana jacks spaced at .75" (19mm).
- Pomona's double banana plugs can be used with most digital multimeters.
- Offset design and color-coded black and red safety shrouds eliminate wrong polarity connections.
- Manufactured to comply with the latest safety standards.
- Molded strain relief increases reliability and durability of the cable.

MATERIALS:

Banana Plugs:

Body: Brass, Nickel Plated.

Springs: Beryllium Copper, Nickel Plated.

Inner Insulation: Polypropylene.

Insulation: Santoprene.

Safety Shrouds: Nylon, black and red.

Cable: RG58C/U, .195 (5,0) O.D., 50 OHMS Color: Black.

Marking: POMONA 6283-C-XX®

RATINGS:

IEC-1010-2-031, Category II, P2 compliant.

Operating Temperature: +55°C (+131°F) Max.

Operating Voltage: 600 VRMS.

ORDERING INFORMATION: Model 6283-C-XX

XX = Cable Length. See current catalog for available lengths.

Ordering Example: 6283-C-12 Cable length is 12" (304,8) Cable is RG58C/U, .195 (5,0) color is black.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6283-C-48](#) [6283-C-36](#) [6283-C-60](#)