



FEATURES:

- Shielded cable to reduce noise
- Provides a quick connection between dual Bantam Jacks
- Dual Bantam Plugs are molded to the cable for optimum durability

MATERIALS:

Plugs – Nickel plated brass

Cable – 4 Conductor shielded twisted pair, PVC jacket and insulation

RATINGS:

Operating Temperature: -20°C to +80°C

Operating Voltage: 300 VRMS Max.

Current: 3.36 Amperes @ 25°C Max.

Nominal Capacitance Shield to Conductor: 250pf

Nominal Capacitance Between Conductors: 150pf

ORDERING INFORMATION: Model 6331-96

Standard Length 96 Inches (2134 mm)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6331-96