


# Model 6340 Deluxe DMM Maxi Test Lead Kit



## FEATURES

- Test probes and leads comply with IEC 61010-031 requirements
- Probes, alligator clips & spade lugs fit directly onto test leads for test versatility
- Test accessories conveniently store in the tri-fold nylon pouch provided
- Compatible with most Fluke, H.P., Tektronix & Wavetek digital multimeters
- Kit contains one set of black and white items below
- Wear indication with double insulated (dual extruded) silicone leads shows white or black inner layer for increased safety.

**USA:** Sales: 800-490-2361  
Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
Fax: 425-446-5844  
**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500  
**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

**Model 6340**  
**Deluxe DMM Maxi Test Lead Kit****MATERIALS**

Model **6261**: Minipincer to Banana Jack: Body: Nylon  
Pincer: Beryllium-Copper, Gold Plated

Wire: 18 AWG, 192 x 41 bare copper, Silicone  
Insulation, O.D. 0.144" (3,66mm). Banana Jack Body  
– Brass, Nickel Plated Insulation – Nylon. **RATINGS**:  
Category II, 300V 5 Amperes

Model **6275**: Precision Electronic Probe: Right Angle  
Sheathed Banana Plug: Plug Body: Nickel plated  
brass. Banana Plug Spring: Nickel Plated Beryllium  
copper. Insulation: Polypropylene, Fire Retardant.  
Wire: 20 AWG, silicon rubber .089 (2,26mm) O.D.,  
Tips: Stainless Steel and one full set of replacement  
tips, see below. **RATINGS**: Operating Temperature;  
55° C., Voltage: CAT II 1000 V, 3 Amperes

Model **6041B**: Large Alligator Clip: Body-Steel, Nickel  
plated, Insulation-Nylon, Color: One Black, One Red,  
**RATINGS**: Voltage: CAT III 1000 V, 10 Amperes

Model **6153**: Spade Lug w/ Jack: ETP 110 Copper,  
1/2 Hard. Finish: Nickel Plated

Model **6252**: Banana Plug Coupler: Brass, Nickel  
Plated, Insulation: Nylon, **RATINGS**: CAT III 1000 V, 10 Amperes

Model **6248**: Minigrabber to Banana Jack: Body: Nylon, Hook: Beryllium Copper, Gold Plated, Wire: 18 AWG,  
Insulation – Silicone, .144", Banana Jack: Body – Brass, Nickel Plated, Insulation – Nylon, **RATINGS**:  
Category II, 300V, 5 Amperes

Model **5907A**: Test Lead Straight to Right Angle: Banana Spring: Nickel plated Beryllium Copper, Insulation –  
Polypropylene, Wire: 48" silicone 18" AWG, Color: One Black, One Red, **RATINGS**: IEC 61010-031, CAT III  
1000 V (with protective cap), CAT II 1000 V (without protective cap), 10 Amperes

Model **5906A**: Modular Probe with Banana Plug Tip: Probe Body: Nylon, Plug Tip: Brass, Nickel Plated, Spring  
– Beryllium Copper, Nickel Plated, 4mm Safety Jack: Brass, Nickel Plated, **RATINGS**: CAT III 1000V, 10  
Amperes

Model **5916A**: Medium Alligator Clip: Body–Steel, Nickel Plated, Color: One Black, One Red, **RATINGS**: CAT I  
300V, 5 Amperes

Model **6354**: Set of 5 Replacement Tips for the Model 6275 Probe



**Model 6340**  
**Deluxe DMM Maxi Test Lead Kit****ORDERING INFORMATION: 6340** (Includes a kit of items from above)

Replacement P/N's:

• Model <b>6041B</b> : Ex-Large Alligator Clip Set
• Model <b>5916A</b> : Medium Alligator Clip Set
• Model <b>6153</b> : Spade Lug
• Model <b>6248-12-*</b> : Minigrabber Jack
• Model <b>5906A</b> : Modular Test Probe Set
• Model <b>5907A</b> : Test Lead Set Straight to Right Angle
• Model <b>6252</b> : Coupler Set
• Model, <b>6261-12-*</b> : Minipincer/Jack
• Model <b>6275</b> : Precision Electronic Probe Set
• Model <b>6354</b> : Set of 5 replacement tips 2 each: Plunger tip, gold plated, 1" & 3" stainless steel Straight tips, 3 point crown tip, plunger, and 4 point plunger tip

\* 0 - Black, 2 - Red    Set = 1 Black, 1 Red

**USA:** Sales: 800-490-2361  
Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
Fax: 425-446-5844  
**Europe:** 31-(0) 40 2675 150    **International:** 425-446-5500  
**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm 0.02$ " (.51 mm),  
.xxx =  $\pm 0.005$ " (.127 mm). All specifications are to the latest revisions.  
Specifications are subject to change without notice. Registered trademarks are  
the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6340