



FEATURES:

- Allows temperature probes with “K” type Mini-Connectors to be used with Digital Multimeters designed with a temperature measurement function from the Banana Jack input.

MATERIALS:

Insulator – Glass filled thermoplastic, color gray

Banana Plugs – Nickel plated, Beryllium Copper springs on a brass body

RATINGS:

Measurement Range – 0 to 220°F. (-18 to 104°C.)

ORDERING INFORMATION: Model 6369

Note: For use in low voltage environments. Do not exceed 30VAC/60VDC.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6369